

MLFB-Ordering data

6SE6400-3TD00-4AD0



Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Number of phases	3 AC	Power connection Power Module	
Line voltage	380 ... 480 V	Version	Pigtail
Rated current	4.5 A	Power connection motor	
Mechanical data		Version	screw terminals
Degree of protection	IP20 / UL open type	Conductor cross-section	2.50 mm ²
Net weight	5.20 kg	Max. motor cable length	
Width	110.0 mm	Shielded	200 m
Height	300.0 mm	Unshielded	300 m
Depth	75.5 mm	PE connection	
		Version	M5 stud
Standards			
		Compliance with standards	cURus