



Figure similar

### MLFB-Ordering data

6SE6400-4BC05-0AA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

### Rated data

|                             |            |
|-----------------------------|------------|
| DC-link voltage, max.       | DC 450.0 V |
| Rated power P <sub>db</sub> | 0.050 kW   |
| Rated power, max.           | 1.00 kW    |

### General tech. specifications

|            |       |
|------------|-------|
| Resistance | 180 Ω |
|------------|-------|

### Mechanical data

|                      |                     |
|----------------------|---------------------|
| Degree of protection | IP20 / UL open type |
| Net weight           | 1.00 kg (2.20 lb)   |
| Width                | 72.0 mm (2.83 in)   |
| Height               | 230.0 mm (9.06 in)  |
| Depth                | 43.5 mm (1.71 in)   |

### Connections

#### Power connection

|         |         |
|---------|---------|
| Version | pigtail |
| Length  | 0.55 m  |

#### PE connection

|                    |              |
|--------------------|--------------|
| Version            | pigtail      |
| Version on housing | M4 stud bolt |

### Thermostatic switch

|         |                         |
|---------|-------------------------|
| Version | Normally closed contact |
|---------|-------------------------|

|                         |                      |
|-------------------------|----------------------|
| Conductor cross-section | 2.50 mm <sup>2</sup> |
|-------------------------|----------------------|