

LV HRC fuse element, NH2, In: 315 A, gG, Un AC: 690 V, Un DC: 440 V, Combined indicator, live grip lugs



Model	
Product brand name	SENTRON
Product designation	LV HRC fuse link
Design of the product	With blade contacts
Design of an identification indicator	Combination alarms
Design of the switching contact	Non-corroding, silver-plated
Design of the fuse link	LV HRC fuse link
General technical data	
Size of fuse system / acc. to DIN EN 60269-1	NH2
Operating class of the fuse link	gG
circuit-breaker / Design	3NA7
Type of voltage	AC/DC
Current / at AC / rated value	315 A
Supply voltage	
• at AC / rated value	690 V
• at DC	440 V
Protection class	
Protection class IP	IP20, with connected conductors

Switching capacity

Switching capacity current

- at DC / acc. to IEC 60947-2 / rated value 25 kA
- acc. to IEC 60947-2 / rated value 120 kA

Dissipation

Power loss [W]	28.1 W
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	28.1 W

Current

Tripping residual / rated value / derated current / at 40 Cel	299.25 A
Diken-export / Let-through energy	DE_3NA_2_690_gG_315

Mechanical Design

Width <ul style="list-style-type: none">• of the enclosure	57.8 mm
Mounting position	Any, preferably vertical
Net weight	588 g

Environmental conditions

Ambient temperature <ul style="list-style-type: none">• during storage	-5 ... +40 °C Air humidity 90% at 20 °C
Environmental category	-20 to +50 at 95% relative humidity

Certificates

Reference code <ul style="list-style-type: none">• acc. to DIN EN 61346-2• acc. to DIN EN 81346-2	F F
--	--------

General Product Approval	Declaration of Conformity	Test Certificates	Shipping Approval
--------------------------	---------------------------	-------------------	-------------------



VDE



EG-Konf.

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

[Miscellaneous](#)



GL

other

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=3NA7252-6>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NA7252-6>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NA7252-6

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



1

-F1



2

