



Figure similar

MLFB-Ordering data

6SE6400-4BD16-5CA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data

DC-link voltage, max.	DC 900.0 V
Rated power P _{db}	0.650 kW
Rated power, max.	13.00 kW

General tech. specifications

Resistance	56 Ω
------------	------

Mechanical data

Degree of protection	IP20 / UL open type
Net weight	3.80 kg (8.38 lb)
Width	185.0 mm (7.28 in)
Height	285.0 mm (11.22 in)
Depth	150.0 mm (5.91 in)

Connections

Power connection

Version	pigtail
Length	0.91 m

PE connection

Version	pigtail
Version on housing	M5 stud bolt

Thermostatic switch

Version	Normally closed contact
---------	-------------------------

Conductor cross-section	2.50 mm ²
-------------------------	----------------------