



Figure similar

MLFB-Ordering data

6SE6400-4BD21-2DA0

Client order no. :

Item no. :

Order no. :

Consignment no. :

Offer no. :

Project :

Remarks :

Rated data		Connections	
DC-link voltage, max.	DC 900.0 V	<b>Power connection</b>	
Rated power P <sub>db</sub>	1.200 kW	Version	M6 screw studs
Rated power, max.	24.00 kW	Conductor cross-section	6.00 mm <sup>2</sup>
General tech. specifications		<b>PE connection</b>	
Resistance	27 Ω	Version	M6 screw studs
		Version on housing	M6 screw studs
Mechanical data		Thermostatic switch	
Degree of protection	IP20 / UL open type	Version	Normally closed contact
Net weight	7.40 kg (16.31 lb)	Conductor cross-section	2.50 mm <sup>2</sup>
Width	270.0 mm (10.63 in)		
Height	515.0 mm (20.28 in)		
Depth	175.0 mm (6.89 in)		