



Figure similar

MLFB-Ordering data

6SE6400-4BD22-2EA1

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
DC-link voltage, max.	DC 900.0 V	Power connection	
Rated power P _{db}	2.200 kW	Version	M6 screw studs
Rated power, max.	44.00 kW	Conductor cross-section	16.00 mm ²
General tech. specifications		PE connection	
Resistance	15 Ω	Version	M6 screw studs
		Version on housing	M6 screw studs
Mechanical data		Thermostatic switch	
Degree of protection	IP20 / UL open type	Version	Normally closed contact
Net weight	11.00 kg (24.25 lb)	Conductor cross-section	2.50 mm ²
Width	326.0 mm (12.83 in)		
Height	301.0 mm (11.85 in)		
Depth	484.0 mm (19.06 in)		