



Figure similar

MLFB-Ordering data

6SE6400-4BD24-0FA0

Client order no. :

Item no. :

Order no. :

Consignment no. :

Offer no. :

Project :

Remarks :

Rated data

DC-link voltage, max.	DC 900.0 V
Rated power P _{db}	4.000 kW
Rated power, max.	80.00 kW

General tech. specifications

Resistance	8 Ω
------------	-----

Mechanical data

Degree of protection	IP20 / UL open type
Net weight	16.70 kg (36.82 lb)
Width	395.0 mm (15.55 in)
Height	650.0 mm (25.59 in)
Depth	315.0 mm (12.40 in)

Connections

Power connection

Version	M6 screw studs
---------	----------------

Conductor cross-section	35.00 mm ²
-------------------------	-----------------------

PE connection

Version	M6 screw studs
---------	----------------

Version on housing	M6 screw studs
--------------------	----------------

Thermostatic switch

Version	Normally closed contact
---------	-------------------------

Conductor cross-section	2.50 mm ²
-------------------------	----------------------