

INSTA contactor with 4 NO contacts Contact for 230 V AC, 400V 40A  
Control 230 V AC 220 V DC



Model	
Product brand name	SETRON
Product designation	Insta contactors
Design of the product	4 NO contacts
Type of voltage / of the operating voltage	AC
Type of voltage / for actuation	AC/DC
Supply voltage	
Current / at AC / rated value	40 A
Operating voltage / rated value	
• minimum	400 V
• maximum	400 V
Protection class	
Protection class IP	IP20
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	4 W
Main circuit	

Operating current / rated value	40 A
---------------------------------	------

### Control current

Control supply voltage	
• rated value	230 V
• rated value / maximum	230 V
• at DC / rated value	220 V

### Product details

Product component / Slide for manual operation	No
Product extension / can be installed / supplementary devices	Yes

### Number

Number of NC contacts	0
Number of NO contacts	4

### Mechanical Design

Height	90 mm
Width	53.5 mm
Depth	71 mm
Installation depth	64 mm
Number of width units	3
Net weight	150 g

### Certificates

Reference code	
• acc. to DIN EN 61346-2	Q
• acc. to DIN EN 81346-2	Q

#### General Product Approval

#### Declaration of Conformity



CCC



UL

[Miscellaneous](#)



EG-Konf.

### Further information

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=5TT5040-0>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TT5040-0>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=5TT5040-0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=5TT5040-0)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://www.siemens.com/specifications>







