

RC unit for 5SY, 2-pole, type F, short-time delayed, In: 63 A, 30 mA,
Un AC: 230 V



Model	
Product brand name	SENTRON
Product designation	RC unit
Design of the product	Short-time delayed
Product variations	for 5SY
General technical data	
Number of poles	2
Size of installation devices / acc. to DIN 43880	1
Protection against electrical shock	Finger and back-of-hand safe
circuit-breaker / Design	5SM2
Mechanical service life (switching cycles) / typical	10 000
Switching function / short-term delayed	Yes
Overvoltage category	III
Supply voltage	
Current / at AC / rated value	63 A
<ul style="list-style-type: none"> • Supply voltage / at AC / rated value • Supply voltage / for testing equipment / minimum 	230 V 195 V

• rated value	50 Hz
Protection class	
Protection class IP	IP20, if the distribution board is installed, with connected conductors
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	4.6 W
Current	
Tripping residual current / rated value	30 mA
Tripping residual / rated value / derated current	
• at 40 Cel	58.59 A
• at 45 Cel	58.59 A
• at 50 Cel	56.7 A
• at 55 Cel	54.81 A
• at 60 Cel	53.55 A
• at 65 Cel	52.29 A
• at 70 Cel	50.4 A
Type of fault current	F
Surge current resistance / rated value	3 kA
Operating frequency	50Hz
Product details	
Product feature / silicon-free	Yes
Product extension / can be installed / supplementary devices	Yes
Connections	
Connectable conductor cross-section	
• solid	1.5 ... 25 mm ²
• stranded	1.5 ... 25 mm ²
Tightening torque / with screw-type terminals	2.5 ... 3 N·m
Position / of power supply cord	top or bottom
Mechanical Design	
Installation depth	70 mm
Number of width units	2
Mounting type	DIN rail (REG)
Mounting position	any
Net weight	214 g
Environmental conditions	
Ambient temperature	-25 ... +45 °C
• during storage	-40 ... +75 °C
Certificates	

General Product Approval	Declaration of Conformity	other
--------------------------	---------------------------	-------



[Miscellaneous](#)



[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SM2325-3>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SM2325-3>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SM2325-3

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



