

SENTRON, cylindrical fuse link, Class CC, 30 A, time-lag, current-limiting, Un AC: 600 V, respect national installation rules!



Model	
Product brand name	SENTRON
Product designation	Cylindrical fuse link
General technical data	
Operating class of the fuse link	Slow, current limiting
Size of the fuse link	Class CC
Type of voltage	AC
Current / at AC / rated value	30 A
Operating voltage / rated value	600 V
Main circuit	
Operating current / Rated value	30 A
Product details	
Product component / striker	No
Mounting position	Any, preferably vertical
Net weight	7 g
Certificates	
Reference code	

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F
F

General Product Approval

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW3300-0HG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW3300-0HG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW3300-0HG

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

