

LV HRC fuse element, NH2, In: 250 A, gG, Un AC: 690 V, Un DC: 440 V, Combined indicator, Insulated grip lugs



Model	
Product brand name	SETRON
Product designation	LV HRC fuse link
Design of the product	With blade contacts
Design of an identification indicator	Combination alarms
Design of the switching contact	Non-corroding, silver-plated
Design of the fuse link	LV HRC fuse link
General technical data	
Size of fuse system / acc. to DIN EN 60269-1	NH2
Operating class of the fuse link	gG
circuit-breaker / Design	3NA6
Type of voltage	AC/DC
Current / at AC / rated value	250 A
Supply voltage	
• at AC / rated value	690 V
• at DC	440 V
Protection class	
Protection class IP	IP20, with connected conductors

## Switching capacity

### Switching capacity current

- |   |        |
|---|--------|
| • at DC / acc. to IEC 60947-2 / rated value | 25 kA  |
| • acc. to IEC 60947-2 / rated value         | 120 kA |

## Dissipation

Power loss [W]	23 W
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	23 W

## Current

Tripping residual / rated value / derated current / at 40 Cel	237.5 A
Diken-export / Let-through energy	DE_3NA_2_690_gG_250

## Mechanical Design



Width	
• of the enclosure	57.8 mm
Mounting position	Any, preferably vertical
Net weight	647 g

## Environmental conditions

Ambient temperature	-5 ... +40 °C
• during storage	Air humidity 90% at 20 °C
Environmental category	-20 to +50 at 95% relative humidity

## Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

Declaration of Conformity	Test Certificates	Shipping Approval	other
 EG-Konf.	<a href="#">Special Test Certificate</a>	<a href="#">Type Test Certificates/Test Report</a>	<a href="#">Miscellaneous</a>
		 GL	<a href="#">Miscellaneous</a>

## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NA6244-6>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)



<https://support.industry.siemens.com/cs/ww/en/ps/3NA6244-6>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NA6244-6](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NA6244-6)

### CAX-Online-Generator

<http://www.siemens.com/cax>



1

-F1



2