

SENTRON, cylindrical fuse holder, 10 x 38 mm, 2-pole, In: 25 A, Ue DC: 1000 V, LED Signal detector, for photovoltaic application



Model	
Product brand name	SENTRON
Product designation	Cylindrical fuse holder
Design of the product	LED signal detector, for photovoltaic applications
General technical data	
Number of poles	2
Size of fuse link	10 x 38 mm
Supply voltage	
Current / at AC / rated value	25 A
Operating voltage	1 000 V
• at DC / rated value	
Protection class IP	IP20
Mechanical Design	
Height	85 mm
Width	36 mm
Depth	65 mm
Net weight	123 g

Certificates

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F
F

General Product Approval	Declaration of Conformity	other
--------------------------	---------------------------	-------



[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7024-4>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW7024-4>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7024-4

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

