

SENTRON, cylindrical fuse holder, 22x58 mm, 3-pole, In: 100 A, Un AC: 690 V



Model	
Product brand name	SENTRON
Product designation	Cylindrical fuse holder
General technical data	
Number of poles	3
Size of fuse link	22 x 58 mm
Supply voltage	
Current / at AC / rated value	100 A
Operating voltage	690 V
• at AC / rated value	
Protection class IP	IP20
Mechanical Design	
Height	117 mm
Width	108 mm
Depth	70 mm
Net weight	503 g
Certificates	

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F
F

Declaration of Conformity

Test Certificates



EG-Konf.

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7231>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW7231>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7231

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





