

SITOR cylindrical fuse link, 22x58 mm, 25 A, aR, Un AC: 690 V, Un DC: 500 V, DC according to UL, Striker indicator



Model	
Product brand name	SETRON
Product designation	SITOR cylindrical fuse link
Design of the product	DC acc. to UL
Design of an identification indicator	Striker indicator
General technical data	
Operating class of the fuse link	aR
Size of the fuse link	22x58 mm
Type of voltage	AC
Current / at AC / rated value	25 A
Supply voltage / at DC	500 V
Operating voltage / rated value	690 V
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	6 W
Main circuit	
Operating current / Rated value	25 A
Product details	

Product component / striker	Yes
Mounting position	Any, preferably vertical
Net weight	41 g

Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

General Product Approval

Declaration of Conformity



UR

[Miscellaneous](#)



EG-Konf.

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC2225-5>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NC2225-5>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2225-5

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



