

MLFB-Ordering data

6SL3202-0AE18-8CA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data

Rated voltage 380.00 ... 480.00 V

Rated current 9.00 A

Power loss 0.080 kW

Mechanical data

Width 207.0 mm (8.15 in)

Height 180.0 mm (7.09 in)

Depth 72.5 mm (2.85 in)

Degree of protection IP20 / UL open type

Net weight 3.90 kg (8.60 lb)

Connections

Power connection motor

Version screw terminals

Conductor cross-section 4.00 mm²

PE connection

Version M4 screw studs