



Figure similar

MLFB-Ordering data

6SL3203-0CD21-4AA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data

Input

Number of phases	3 AC
Line voltage	380 ... 480 V

Output

Rated current	11.6 A
---------------	--------

Mechanical data

Dimensions

Width	153.0 mm (6.0 in)
Height	270.0 mm (10.6 in)
Depth	70.0 mm (2.8 in)
Degree of protection	IP20 / UL open type
Net weight	3.4 kg (7.5 lb)

Connections

Line side

Version	screw-type terminal
---------	---------------------

Load side

Version	Cable
Conductor cross-section	1.50 mm ² (16 AWG)
Cable length	0.46 m (1.51 ft)

PE connection

Version	M5 screw studs
---------	----------------

Standards

Compliance with standards	cURus
---------------------------	-------