

INSTA contactor with 2 NO contacts and 2 NC Contact for 230 V AC, 400V 25A Control 230 V AC 220 V DC



| Model   |                             |
|---|-----------------------------|
| Product brand name  | SETRON                      |
| Product designation   | Insta contactors            |
| Design of the product   | 2 NO contacts 2 NC contacts |
| Type of voltage / of the operating voltage  | AC                          |
| Type of voltage / for actuation   | AC/DC                       |
| Supply voltage  |                             |
| Current / at AC / rated value   | 24 A                        |
| Operating voltage / rated value   |                             |
| • minimum   | 400 V                       |
| • maximum   | 400 V                       |
| Protection class  |                             |
| Protection class IP   | IP20                        |
| Dissipation   |                             |
| Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole | 2.2 W                       |
| Main circuit  |                             |

|                                 |      |
|---------------------------------|------|
| Operating current / rated value | 24 A |
|---------------------------------|------|

### Control current

|                         |       |
|-------------------------|-------|
| Control supply voltage  |       |
| • rated value           | 230 V |
| • rated value / maximum | 230 V |
| • at DC / rated value   | 220 V |

### Product details

|  |     |
|--|-----|
| Product component / Slide for manual operation               | No  |
| Product extension / can be installed / supplementary devices | Yes |

### Number

|                       |   |
|-----------------------|---|
| Number of NC contacts | 2 |
| Number of NO contacts | 2 |

### Mechanical Design

|                       |       |
|-----------------------|-------|
| Height                | 90 mm |
| Width                 | 35 mm |
| Depth                 | 71 mm |
| Installation depth    | 64 mm |
| Number of width units | 2     |
| Net weight            | 150 g |

### Certificates

|                          |   |
|--------------------------|---|
| Reference code           |   |
| • acc. to DIN EN 61346-2 | Q |
| • acc. to DIN EN 81346-2 | Q |

#### General Product Approval

#### Declaration of Conformity



CCC



UL

[Miscellaneous](#)



EG-Konf.

### Further information

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=5TT5032-0>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TT5032-0>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=5TT5032-0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=5TT5032-0)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://www.siemens.com/specifications>







