

Data sheet for Line filter

MLFB-Ordering data

6SE6400-2FA00-6AD0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Input		Line side	
Number of phases	3 AC	Version	screw-type terminal
Line voltage	200 ... 480 V	Conductor cross-section	1,0 ... 2,5 mm ²
Output		Load side	
Rated current	6.0 A	Version	Pigtail
		Cable length	0.46 m
Mechanical data		PE connection	
Dimensions		Version	M4 stud
Width	73.0 mm	Standards	
Height	200.0 mm	Compliance with standards	CE / UL
Depth	43.5 mm		
Degree of protection	IP20 / UL open type		
Net weight	0.5 kg		