

MLFB-Ordering data

6SL3202-0AE24-6SA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Number of phases	3 AC	Power connection Power Module	
Line voltage	380 ... 480 V	Version	screw-type terminal
Rated current	47.0 A	Conductor cross-section	50.00 mm ²
Power loss	0.185 kW	Power connection motor	
Mechanical data		Version	screw terminals
Degree of protection	IP00	Conductor cross-section	50.00 mm ²
Net weight	24.00 kg	Max. motor cable length	
Width	250.0 mm	Shielded	200 m
Height	315.0 mm	Unshielded	300 m
Depth	262.0 mm	PE connection	
		Version	M6 screw