

Circuit breaker Universal current 220 V DC 230/400 V AC 10kA, 1-pole, C, 13A



| Model | |
|--|---------------------------|
| Product brand name | SENTRON |
| Product designation | Miniature circuit breaker |
| General technical data | |
| Number of poles | 1 |
| Number of poles / Note | 1P |
| Tripping characteristic class | C |
| circuit-breaker / Design | 5SY5 |
| Mechanical service life (switching cycles) / typical | 10 000 |
| Overvoltage category | III |
| Voltage | |
| Insulation voltage | |
| • at DC / rated value | 250 V |
| • with single-phase operation / at AC / rated value | 440 V |
| • with multi-phase operation / at AC / rated value | 440 V |
| Supply voltage / with single-phase operation / at AC / rated value | 230 V |

| Supply voltage | |
|--|----------------|
| Type of voltage | AC/DC |
| Current / at AC / rated value | 13 A |
| Supply voltage | |
| <ul style="list-style-type: none"> • at AC / rated value • at DC / rated value | 400 V 220 V |
| Operating voltage | |
| <ul style="list-style-type: none"> • at DC / rated value / maximum | 250 V |
| Supply voltage frequency | |
| <ul style="list-style-type: none"> • rated value | 50/60 Hz |

| Protection class | |
|---------------------|---------------------------------|
| Protection class IP | IP20, with connected conductors |

| Switching capacity | |
|---|----------------|
| Switching capacity current | |
| <ul style="list-style-type: none"> • at DC / acc. to IEC 60947-2 / rated value • acc. to EN 60898 / rated value | 15 kA 10 kA |
| Energy limiting class | 3 |

| Dissipation | |
|---|-------|
| Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole | 1.4 W |

| Current | |
|---|-------------------|
| Tripping residual / rated value / derated current / at 40 Cel | 12.38 A |
| Suitability for operation | universal current |

| Product details | |
|--|--------------------------|
| Product function / neutral conductor switching | No |
| Product feature / Touch protection | Yes |
| Product component | |
| <ul style="list-style-type: none"> • combined terminal top • combined terminal bottom | Yes Yes |
| Product feature | |
| <ul style="list-style-type: none"> • Properties for main switches in accordance with EN 60204-1 • halogen-free • sealable • silicon-free | Yes Yes Yes Yes |
| Product extension / can be installed / supplementary devices | Yes |

| Short circuit | |
|--|-------|
| Breaking capacity short-circuit current (I _{cn}) | |
| <ul style="list-style-type: none"> • at DC / acc. to EN 60898-2 | 10 kA |

Connections

| | |
|--|---|
| <ul style="list-style-type: none"> • Connectable conductor cross-section <ul style="list-style-type: none"> — solid — stranded • Connectable conductor cross-section / finely stranded / with core end processing | 0.75 ... 35 mm ² 0.75 ... 35 mm ² 0.75 ... 25 mm ² |
| AWG number / as coded connectable conductor cross section | 18 ... 4 |
| Tightening torque [lbf·in] / with screw-type terminals | 22 ... 31 lbf·in |
| Tightening torque / with screw-type terminals | 2.5 ... 3.5 N·m |
| Position / of power supply cord | AC as required, observe DC polarity |

Mechanical Design

| | |
|-----------------------|-----------------------|
| Height | 90 mm |
| Width | 18 mm |
| Depth | 76 mm |
| Installation depth | 70 mm |
| Number of width units | 1 |
| Mounting type | Quick assembly system |
| Mounting position | any |
| Net weight | 169 g |

Environmental conditions

| | |
|--|--|
| Influence of the surrounding temperature | max. 95% to 55°C, max. 55% to 70°C, max. 35% to 75°C |
| Ambient temperature <ul style="list-style-type: none"> • during storage | -40 ... +70 °C -40 ... +75 °C |

Certificates

| | |
|---|--------|
| Reference code <ul style="list-style-type: none"> • acc. to DIN EN 61346-2 • acc. to DIN EN 81346-2 | F F |
|---|--------|

General Product Approval

Declaration of Conformity

Test Certificates



[Miscellaneous](#)



[Miscellaneous](#)

Railway

[Confirmation](#)

[Vibration and Shock](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SY5113-7>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SY5113-7>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SY5113-7

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



