

RC unit for 5SL4, 2-pole, type A, In: 63 A, 30 mA, Un AC: 230 V



Model	
Product brand name	SENTRON
Product designation	RC unit
Design of the product	Instantaneous
Product variations	for 5SL4
General technical data	
Number of poles	2
Size of installation devices / acc. to DIN 43880	1
Protection against electrical shock	Finger and back-of-hand safe
circuit-breaker / Design	5SM2
Mechanical service life (switching cycles) / typical	10 000
Switching function / short-term delayed	No
Overvoltage category	III
Supply voltage	
Current / at AC / rated value	63 A
<ul style="list-style-type: none"> <li>• Supply voltage / at AC / rated value</li> <li>• Supply voltage / for testing equipment / minimum</li> </ul>	<p>230 V</p> <p>195 V</p>

- rated value

50 Hz

### Protection class

Protection class IP

IP20, if the distribution board is installed, with connected conductors

### Dissipation

Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole

4.6 W

### Current

Tripping residual current / rated value

30 mA

Tripping residual / rated value / derated current

• at 40 Cel	58.59 A
• at 45 Cel	58.59 A
• at 50 Cel	56.7 A
• at 55 Cel	54.81 A
• at 60 Cel	53.55 A
• at 65 Cel	52.29 A
• at 70 Cel	50.4 A

Type of fault current

A

Surge current resistance / rated value

1 kA

Operating frequency

50Hz

### Product details

Product feature / silicon-free

Yes

Product extension / can be installed / supplementary devices

Yes

### Connections

Connectable conductor cross-section

• solid	1.5 ... 25 mm <sup>2</sup>
• stranded	1.5 ... 25 mm <sup>2</sup>

Tightening torque / with screw-type terminals

2.5 ... 3 N·m

Position / of power supply cord

top or bottom

### Mechanical Design

Height

90 mm

Width

70 mm

Depth

70 mm

Installation depth

70 mm

Number of width units

2

Mounting type

DIN rail (REG)

Mounting position

any

Net weight

210 g

### Environmental conditions

Ambient temperature

- during storage

-25 ... +45 °C

-40 ... +75 °C

## Certificates

General Product Approval

Declaration of  
Conformity

other



CCC



VDE

[Miscellaneous](#)



EG-Konf.

[Miscellaneous](#)

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SM2326-6>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5SM2326-6>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SM2326-6](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SM2326-6)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



