

shunt release 24-48 V DC, for miniature circuit breaker 5SL4, 5SY, 5SP, RCBO 5SU1, FI 5SV (for 5SU1 handle coupler 5ST3805-1 is required)



Model	
Product brand name	SENTRON
Product designation	Shunt trip
Design of the product	Mountable
Electrical endurance (switching cycles) / typical	20 000
Supply voltage	
Operating voltage	
• rated value	230 V
Protection class IP	IP20
Product details	
Product extension	shunt trip
Number	
Number of fault signal contacts	0
Number of NC contacts	2
Number of NO contacts	0
Number of CO contacts	0
Connections	

Connectable conductor cross-section	0.5 ... 2.5 mm ²
Tightening torque / with screw-type terminals	0.5 N·m
Type of connectable conductor cross-sections / at AWG conductors	24 ... 12

Mechanical Design

Height	90 mm
Width	18 mm
Depth	70 mm
Net weight	90 g
<ul style="list-style-type: none"> during operation during storage 	-25 ... +55 °C -40 ... +75 °C

Certificates

Declaration of Conformity	other	Railway
---------------------------	-------	---------



EG-Konf.

[Environmental Confirmations](#)

[Miscellaneous](#)

[Vibration and Shock](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5ST3031>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5ST3031>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5ST3031

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





