

**CD-HF 50X100 5/7.5 DKG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Similar to illustration**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source. The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

**General ordering data**

Type	CD-HF 50X100 5/7.5 DKG
Order No.	<a href="#">2589320000</a>
Version	Halogen-free cable duct, 50 mm x 100 mm, 5.00 mm x 7.50 mm, 2000 mm
GTIN (EAN)	4050118602647
Qty.	16 m

**CD-HF 50X100 5/7.5 DKG Y**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	2,000 mm	Length (inches)	78.74 inch
Width	100 mm	Width (inches)	3.937 inch
Height	50 mm	Height (inches)	1.969 inch
Net weight	700 g		

**General information**

Colour	dark grey	Cover	Yes
Flexible wiring duct	No	Halogen	No
Material	PPE	Non-tracking	Yes
Slit gap	7.5 mm	Slit width	5 mm
Type of mounting	when screwed in, With adhesive, Riveted	UL 94 flammability rating	V-0
Usable cross-section	4,180 mm <sup>2</sup>	Version of side panel	slotted

**Classifications**

ETIM 6.0	EC000012	eClass 6.2	27-40-07-03
eClass 9.1	27-40-07-03		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Engineering Data [STEP](#)

**Data sheet**

**CD-HF 50X100 5/7.5 DKG Y**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

