

CD-HF 75X125 5/7.5 DKG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

Increase your wiring flexibility with our comprehensive range of accessories available from a single source. The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sized holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

Type	CD-HF 75X125 5/7.5 DKG
Order No.	2589270000
Version	Halogen-free cable duct, 75 mm x 125 mm, 5.00 mm x 7.50 mm, 2000 mm
GTIN (EAN)	4050118603613
Qty.	12 m

CD-HF 75X125 5/7.5 DKG Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	2,000 mm	Length (inches)	78.74 inch
Width	125 mm	Width (inches)	4.921 inch
Height	75 mm	Height (inches)	2.953 inch
Net weight	825 g		

General information

Colour	dark grey	Cover	Yes
Flexible wiring duct	No	Halogen	No
Material	PPE	Non-tracking	Yes
Slit gap	7.5 mm	Slit width	5 mm
Type of mounting	when screwed in, With adhesive, Riveted	UL 94 flammability rating	V-0
Usable cross-section	7,115 mm ²	Version of side panel	slotted

Classifications

ETIM 6.0	EC000012	eClass 6.2	27-40-07-03
eClass 9.1	27-40-07-03		

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data [STEP](#)

CD-HF 75X125 5/7.5 DKG Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

