

CD-BO 60X80 8/12 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

Type	CD-BO 60X80 8/12 GY
Order No.	258980000
Version	Cable duct floor duct, 60 mm x 80 mm, 8.00 mm x 12.00 mm, 2000 mm
GTIN (EAN)	4050118600957
Qty.	24 m

CD-BO 60X80 8/12 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Length	2,000 mm	Length (inches)	78.74 inch
Width	80 mm	Width (inches)	3.15 inch
Height	60 mm	Height (inches)	2.362 inch
Net weight	750 g		

General information

Colour	grey	Cover	Yes
Flexible wiring duct	No	Halogen	Yes
Material	PVC	Non-tracking	Yes
Slit gap	12 mm	Slit width	8 mm
Type of mounting	when screwed in, With adhesive, Riveted	UL 94 flammability rating	V-0
Usable cross-section	4,200 mm ²	Version of side panel	slotted

Classifications

ETIM 6.0	EC000012	eClass 6.2	27-40-07-03
eClass 9.1	27-40-07-03		

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data

[STEP](#)

CD-BO 60X80 8/12 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

