

**CD-HF 37.5X37.5 5/7.5 DKG Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Increase your wiring flexibility with our comprehensive range of accessories available from a single source. The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sized holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

**General ordering data**

Type	CD-HF 37.5X37.5 5/7.5 DKG Y
Order No.	<a href="#">2590040000</a>
Version	Halogen-free cable duct, 37.5 mm x 37.5 mm, 5.00 mm x 7.50 mm, 2000 mm
GTIN (EAN)	4050118603415
Qty.	48 m

**CD-HF 37.5X37.5 5/7.5 DKG Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

Length	2,000 mm	Length (inches)	78.74 inch
Width	37.5 mm	Width (inches)	1.476 inch
Height	37.5 mm	Height (inches)	1.476 inch
Net weight	277 g		

**General information**

Colour	dark grey	Cover	Yes
Flexible wiring duct	No	Halogen	No
Material	PPE	Non-tracking	Yes
Slit gap	7.5 mm	Slit width	5 mm
Type of mounting	when screwed in, With adhesive, Riveted	UL 94 flammability rating	V-0
Usable cross-section	1,125 mm <sup>2</sup>	Version of side panel	slotted

**Classifications**

ETIM 6.0	EC000012	eClass 6.2	27-40-07-03
eClass 9.1	27-40-07-03		

**Approvals**

Approvals



ROHS

Conform

**Downloads**

Engineering Data

[STEP](#)

**Data sheet**

**CD-HF 37.5X37.5 5/7.5 DKG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

