


## Crocodile clips

### MA 2 VA



| Product  | MA 2 VA   |
|--|---|
| description  | Miniature alligator clip with high strength insulation and 2 mm socket connection. Jaws and spring in stainless steel. The flat part of the jaws (fine wire section) allows a secure contact to be made when clamping even the thinnest wires. Capable of clamping flat components (soldering eyes) and wires up to a maximum diameter of 4 mm. |
| article-no. / *colour  | 9303191xx<br><br>00 black    01 red    02 blue    03 yellow    04 green    06 gray    07 white  |
| <b>technical data</b>  |   |
| connection   | 2 mm socket   |
| rated voltage <sup>(1)</sup>   | 30 VAC / 60 VDC   |
| measurement cat. acc. to IEC 61010   | O <sup>(3)</sup>  |
| rated current <sup>(1)</sup><br>(consider derating curve)                      | 6 A   |
| material socket  | stainless steel   |
| housing material   | PP  |
| temperature range acc. To IEC61010 <sup>(2)</sup>                              | -25 °C to 70 °C   |
| flammability class acc. to UL 94<br>(only valid for basic material of housing) | HB  |
| clamping range   | 4 mm  |
| standard   | IEC 61010   |

2 mm system

<sup>(1)</sup> for normal environmental conditions -5°C to +40°C

<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges

<sup>(3)</sup> Other circuits that are not directly connected to mains

stand: 27.07.2018