

# H05V-K / (H)07V-K PVC-single cores, fine wire stranded, 2-colour



Cross-sec. mm <sup>2</sup>	Outer Ø min. - max. mm	Cop. weight kg / km	RD/WH	BU/WH	BN/WH	D-BU/WH
----------------------------	------------------------	---------------------	-------	-------	-------	---------



## Packing

### Coil in cardboard (100m)

H05V-K coil			RD/WH	BU/WH	BN/WH	D-BU/WH
Part no.			29370	29375	29380	29394
0,5	2,1 - 2,5	4,8				
Part no.			29371	29376	29381	29395
0,75	2,2 - 2,7	7,2				
Part no.			29372	29377	29382	29396
1	2,4 - 2,8	9,6				

## Packing

### Coil in cardboard (100m)

(H)07V-K coil			RD/WH	BU/WH	BN/WH	D-BU/WH
Part no.			29373	29378	29383	29397
1,5	2,8 - 3,4	14,4				
Part no.			29374	29379	29384	29398
2,5	3,4 - 4,1	24,0				
Part no.			29385	29386	29387	29399
4	3,9 - 4,8	38,0				
Part no.			29388	29389	29390	29527
6	4,4 - 5,3	58,0				
Part no.			29391	29392	29393	29528
10	5,7 - 6,8	96,0				



## Packing

### Spool (with various capacity)

H05V-K spool			RD/WH	BU/WH	BN/WH	D-BU/WH
Part no.			29745	29746	29747	29748
0,5	2,1 - 2,5	4,8				
Part no.			29749	29750	29751	29752
0,75	2,2 - 2,7	7,2				
Part no.			29753	29754	29755	29756
1	2,4 - 2,8	9,6				

## Packing

### Spool (with various capacity)

(H)07V-K spool			RD/WH	BU/WH	BN/WH	D-BU/WH
Part no.			29757	29758	29759	29760
1,5	2,8 - 3,4	14,4				
Part no.			29761	29762	29763	29764
2,5	3,4 - 4,1	24,0				
Part no.			29765	29766	29767	29768
4	3,9 - 4,8	38,0				
Part no.			29769	29770	29771	29772
6	4,4 - 5,3	58,0				
Part no.			29773	29774	29775	29776
10	5,7 - 6,8	96,0				



## Packing

### Barrel (with various capacity)

H05V-K barrel			RD/WH	BU/WH	BN/WH	D-BU/WH
Part no.			28948	28949	28950	28951
0,5	2,1 - 2,5	4,8				
Part no.			28952	28953	28954	28955
0,75	2,2 - 2,7	7,2				
Part no.			28956	28957	28958	28959
1	2,4 - 2,8	9,6				

## Packing

### Barrel (with various capacity)

(H)07V-K barrel			RD/WH	BU/WH	BN/WH	D-BU/WH
Part no.			28960	28961	28962	28963
1,5	2,8 - 3,4	14,4				
Part no.			28964	28965	28966	28967
2,5	3,4 - 4,1	24,0				
Part no.			28968	28969	28970	28971
4	3,9 - 4,8	38,0				
Part no.			28972	28973	28974	28975
6	4,4 - 5,3	58,0				
Part no.			28976	28977	28978	28979
10	5,7 - 6,8	96,0				

Dimensions and specifications may be changed without prior notice.