

SAIH-3x0,25(PVC)

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Weidmüller offers a large and comprehensive range of sensor-actuator cables. We provide both, sensor cables as well as bus and valve cables of various sizes and lengths. If you cannot find a specific product or a product in the desired length, just contact us.

General ordering data

Type	SAIH-3x0,25(PVC)
Order No.	1902190000
Version	Sensor/actuator line, Number of poles : 3, Shielded: No, Sheath material: PVC, Halogen: Yes
GTIN (EAN)	4032248516049
Qty.	100 m

SAIH-3x0,25(PVC)**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 28.01 g

Technical specifications for cable

Number of poles	3	Core cross-section	0.25 mm ²
Outside diameter	4.5 ± 0.2 mm	Shielded	No
Insulation	PVC	Colour coding	brown, blue, black
Sheath material	PVC	Sheathing colour	black
Halogen	Yes	Temperature range, moving	-5...80 °C
Temperature range, stationary	-30...80 °C	Outer cladding in accordance with UL AWM style	2464 (80 °C / 300 V)
Suitable for cable carriers	No	Torsion resistance	0 °/m
Resistant to welding beads	No	Hybrid cable	No
Irradiation crosslinked	No	Configurable cable length	No

Classifications

ETIM 3.0	EC000830	ETIM 4.0	EC000830
ETIM 5.0	EC000830	ETIM 6.0	EC001855
UNSPSC	26-12-16-13	eClass 5.1	27-06-91-90
eClass 6.2	27-06-91-90	eClass 7.1	27-06-91-90
eClass 8.1	27-06-91-90	eClass 9.0	27-06-03-11
eClass 9.1	27-06-90-90		

Approvals

Approvals



ROHS

Conform

Downloads

Brochure/Catalogue	CAT 8 SAI 15/16 EN FL FIELDWIRING EN
Engineering Data	WSCAD