

**SAIH-PB-PA-2X1.0-PVC-BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Weidmüller offers a large and comprehensive range of sensor-actuator cables. We provide both, sensor cables as well as bus and valve cables of various sizes and lengths. If you cannot find a specific product or a product in the desired length, just contact us.

**General ordering data**

Type	SAIH-PB-PA-2X1.0-PVC-BL
Order No.	<a href="#">1232630000</a>
Version	Bus line, No. of poles: 2, Shielded: Yes, LED: No, Sheath material: PVC, Halogen: Yes
GTIN (EAN)	4050118016505
Qty.	100 m

**SAIH-PB-PA-2X1.0-PVC-BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 80.4 g

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Technical specifications for cable**

Number of poles	2	Core cross-section	1 mm <sup>2</sup>
Outside diameter	8 ± 0.4 mm	Shielded	Yes
Insulation	PE	Colour coding	red, green
Sheath material	PVC	Sheathing colour	blue (RAL 5015)
Halogen	Yes	Temperature range, moving	-5...60 °C
Temperature range, stationary	-30...80 °C	Suitable for cable carriers	No
Bending radius, min., stationary	8 x Kabeldurchmesser	Bending radius, min., moving	8 x Kabeldurchmesser
Resistant to welding beads	No	Hybrid cable	No
Irradiation crosslinked	No	Configurable cable length	No

**Classifications**

ETIM 6.0	EC000830	eClass 6.2	27-06-91-90
eClass 7.1	27-06-91-90	eClass 8.1	27-06-91-90
eClass 9.0	27-06-18-05	eClass 9.1	27-06-90-90

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue [CAT 8 SAI 15/16 EN](#)  
[FL FIELDWIRING EN](#)