

HS 8.5-25.4/25 MM W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**MultiMark**

With MultiMark you have a fast and reliable marking system at your disposal to enable virtually any kind of marking. Connectors, conductors, cables or devices – the MultiMark product family offers a well-structured, practical range of markers which can be used in combination with our advanced M-Print® PRO configuration software for all areas of use.

Your benefits with MultiMark

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

General ordering data

Type	HS 8.5-25.4/25 MM W
Order No.	2437790000
Version	Conductor and cable markers, 8.5 - 25.4 mm, 25.4 x 40.5 mm, white
GTIN (EAN)	4050118460957
Qty.	400 pc(s).
compatible printer	2430920000 2448870000 1140490000

HS 8.5-25.4/25 MM W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Width	40.5 mm	Width (inches)	1.594 inch
Height	25.4 mm	Height (inches)	1 inch
Depth	0.77 mm	Depth (inches)	0.03 inch
Net weight	1.6 g		

General data

Colour	white	Halogen	Yes
Material	Polyolefine	Number per roll	400
Operating temperature range	-55...135 °C	Recommended industries	Plant manufacture, Energy, Device manufacturer, Machinery
Width	40.5 mm		

Conductor and cable markers

Conductor O.D.	8.5 - 25.4 mm	Conductor O.D., max.	25.4 mm
Conductor O.D., min.	8.5 mm	Conductor cross-section, max.	120 mm ²
Conductor cross-section, min.	35 mm ²	Halogen	Yes
Rate of shrinkage	3:1	Recommended shrinking temperature	90 °C

Classifications

ETIM 5.0	EC001530	ETIM 6.0	EC001530
eClass 6.2	27-40-04-01	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN
------------------	-----------------------

HS 8.5-25.4/25 MM W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

