

**SKMU PA (plastic locknut)
SKMU M40 K SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Weidmüller has a variety of different cable and wire entry systems in the Portfolio: with different designs of plastic, brass and stainless steel cable glands in the IP66, 67, 68 or IP69k protection classes. As a complete alternative to cable glands, pre-assembled cables with modular multi-wire or multi-cable entry systems can be simply and quickly inserted into electrical equipment. Last but not least, Weidmüller offers EX-certified cable glands and cable/wire entry systems.

- Cable glands made from plastic and brass
- EMC screwed joints
- for areas at risk of explosion
- VDE, CSA and UL approvals

General ordering data

Type	SKMU M40 K SW
Order No.	1736960000
Version	SKMU PA (plastic locknut), Locknut, M 40, 7 mm, Polyamid 6 (PA6 - GF30)
GTIN (EAN)	4008190956431
Qty.	10 pc(s).

SKMU PA (plastic locknut)
SKMU M40 K SW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Net weight 1.92 g

Width

Thickness 7 mm

General information

AF size 1	50 mm	Cable glands	metric
External thread	M 40	Internal thread	M 40
Length of thread	7 mm	Material	Polyamid 6 (PA6 - GF30)
O.D.	57.75 mm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-20 °C	Pitch of thread	1.5 mm
Thickness	7 mm	UL 94 flammability rating	V-2

Classifications

ETIM 3.0	EC000940	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000940
UNSPSC	30-21-18-01	eClass 5.1	23-11-07-01
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09
eClass 8.1	27-14-91-09	eClass 9.0	27-14-44-24
eClass 9.1	27-14-44-24		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN.WSCAD
Engineering Data	STEP

SKMU PA (plastic locknut) SKMU M40 K SW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

