

**SAIH-4x0,34(PVC)****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Weidmüller offers a large and comprehensive range of sensor-actuator cables. We provide both, sensor cables as well as bus and valve cables of various sizes and lengths. If you cannot find a specific product or a product in the desired length, just contact us.

**General ordering data**

Type	SAIH-4x0,34(PVC)
Order No.	<a href="#">1902180000</a>
Version	Sensor/actuator line, Number of poles : 4, Shielded: No, Sheath material: PVC, Halogen: Yes
GTIN (EAN)	4032248516025
Qty.	100 m

**SAIH-4x0,34(PVC)****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 41.55 g

**Technical specifications for cable**

Number of poles	4	Core cross-section	0.34 mm <sup>2</sup>
Outside diameter	5.3 ± 0.2 mm	Shielded	No
Insulation	PVC	Colour coding	brown, white, blue, black
Sheath material	PVC	Sheathing colour	black
Halogen	Yes	Temperature range, moving	-5...80 °C
Temperature range, stationary	-30...80 °C	Outer cladding in accordance with UL AWM style	2464 (80 °C / 300 V)
Suitable for cable carriers	No	Torsion resistance	0 °/m
Resistant to welding beads	No	Hybrid cable	No
Irradiation crosslinked	No	Configurable cable length	No

**Classifications**

ETIM 3.0	EC000830	ETIM 4.0	EC000830
ETIM 5.0	EC000830	ETIM 6.0	EC001855
UNSPSC	26-12-16-13	eClass 5.1	27-06-91-90
eClass 6.2	27-06-91-90	eClass 7.1	27-06-91-90
eClass 8.1	27-06-91-90	eClass 9.0	27-06-03-11
eClass 9.1	27-06-90-90		

**Approvals**

Approvals



ROHS

Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 8 SAI 15/16 EN</a> <a href="#">FL FIELDWIRING EN</a>
Engineering Data	<a href="#">WSCAD</a>