

Industrial Ethernet IE-KSF-PKV14M-KLROB-1.5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Assembled IE cables

General ordering data

Type	IE-KSF-PKV14M-KLROB-1.5M
Order No.	1103660015
Version	
GTIN (EAN)	4032248922512
Qty.	1 pc(s).

Industrial Ethernet IE-KSF-PKV14M-KLROB-1.5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	293.6 g
------------	---------

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C	Storage temperature	
Installation temperature			

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Electrical properties

Operating voltage	30 V
-------------------	------

Standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
--------------------	--

Cable structure

Sheath diameter, max.	9.5 mm	Sheathing colour	black (similar to RAL 9005)
-----------------------	--------	------------------	-----------------------------

Electrical properties of cable

Operating voltage	30 V
-------------------	------

Mechanical and material properties of cable

Min. bending radius, once only	5 x cable diameter	Min. bending radius, repetitive	10 x cable diameter
--------------------------------	--------------------	---------------------------------	---------------------

Classifications

ETIM 4.0	EC000385	ETIM 5.0	EC000385
ETIM 6.0	EC000993	eClass 6.2	27-06-03-90
eClass 7.1	27-06-18-01	eClass 8.1	27-06-18-01
eClass 9.0	27-06-20-01	eClass 9.1	27-06-90-90

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	FL FIELDWIRING EN PI PROFINET CABLING EN
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN

Industrial Ethernet IE-KSF-PKV14M-KLROB-1.5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

