

**KSPMH (Klippon blanking plug, type MH)
KSPMH M16 SSC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Type	KSPMH M16 SSC
Order No.	1477820000
Version	KSPMH (Klippon blanking plug, type MH), Blanking plug, M 16, 16 mm, Stainless steel 1.4404 (316L)
GTIN (EAN)	4050118285802
Qty.	20 pc(s).

Data sheet

**KSPMH (Klippon blanking plug, type MH)
KSPMH M16 SSC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	21.5 mm	Length (inches)	0.846 inch
Net weight	38.75 g		

Temperatures

Operating temperature range, max.	200 °C	Operating temperature range, min.	-60 °C
Operating temperature, max.	200 °C	Operating temperature, min.	-60 °C

Classifications

ETIM 6.0	EC000451	eClass 6.2	27-14-92-01
eClass 7.1	27-14-92-01	eClass 8.1	27-14-92-01
eClass 9.0	27-14-44-25	eClass 9.1	27-14-44-35

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP