# SAI-ADAPTER-M8/M8-3P/4P

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



M8/M12 and M12/M8 adapters serve for quick implementation of the plug size.

## General ordering data

| | |
|---|---|
| Type | SAI-ADAPTER-M8/M8-3P/4P |
| Order No. | 1288000000 |
| Version | Y connector, M8 / M8 |
| GTIN (EAN) | 4050118079173 |
| Qty. | 1 pc(s). |

# SAI-ADAPTER-M8/M8-3P/4P

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

## Technical data

### Dimensions and weights

| | |
|---|---|
| Net weight | 8 g |

### Environmental Product Compliance

| | |
|---|---|
| REACH SVHC | Lead 7439-92-1 |

### Connection data

| | | | |
|---|---|---|---|
| Single outlet 1 - plug-in connector | M8 pin | Single outlet 2 - plug-in connector | M8 socket |
| Tightening torque | M8: 0.5 Nm | | |

### General data

| | | | |
|---|---|---|---|
| Coding | M8 = none | Conductor O.D. | - |
| Connection thread | M8 / M8 | Pollution severity | 3 |
| Protection degree | IP67 | Rated current | 4 A |
| Rated voltage | 24 V | Shield connection | No |
| Temperature range of housing | -25...+85 °C | | |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 6.0 | EC002925 | eClass 6.2 | 27-06-91-90 |
| eClass 7.1 | 27-06-91-90 | eClass 8.1 | 27-06-91-90 |
| eClass 9.0 | 27-44-01-06 | eClass 9.1 | 27-44-01-06 |

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |

### Downloads

| | |
|---|---|
| Brochure/Catalogue | FL FIELDWIRING EN |

# SAI-ADAPTER-M8/M8-3P/4P

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

## Drawings

### Dimensioned drawing




