

JACKPAC JP TEST

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



The following products are available as functional components:

- Switch and button components in a sealed built-in EG2 enclosure
- Rectifier and fuse components in a sealed built-in EG2 enclosure
- Logic components with AND, NAND, OR and NOR operators
- Diode gates with up to 40 inputs in open design
- Components modules for the integration of electronic elements
- Serial interface converter, and AD / DA converter

General ordering data

Type	JP TEST
Order No.	8794120000
Version	JACKPAC, Relays, Rated control voltage: 18...24...30 V DC, Continuous current: 2 A, M12 plug/socket, A-coded
GTIN (EAN)	4032248483969
Qty.	1 pc(s).

**JACKPAC
JP TEST**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	83 mm	Length (inches)	3.268 inch
Width	36 mm	Width (inches)	1.417 inch
Height	14.4 mm	Height (inches)	0.567 inch
Net weight	36 g		

Temperatures

Operating temperature, max.	55 °C	Operating temperature, min.	0 °C
Storage temperature, max.	70 °C	Storage temperature, min.	-25 °C
Operating temperature	0 °C...55 °C	Ambient temperature	0 °C...+55 °C
Storage temperature	-25 °C...70 °C		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Input

Rated control voltage	24 V DC ± 25 %	Rated current DC	2.2 mA (LED)
Status indicator	Green LED		

Control side

Rated control voltage	18...24...30 V DC	Status indicator	Green LED
-----------------------	-------------------	------------------	-----------

Output

Continuous current 2 A

Load side

Continuous current 2 A

General data

Colour grey

Insulation coordination

Protection degree IP67

Connection data

Wire connection method M12 plug/socket, A-coded

Classifications

ETIM 3.0	EC001134	ETIM 4.0	EC001134
ETIM 5.0	EC001134	ETIM 6.0	EC001437
UNSPSC	30-21-18-01	eClass 6.2	27-20-11-90
eClass 7.1	27-20-11-90	eClass 8.1	27-20-11-90
eClass 9.0	27-37-16-01	eClass 9.1	27-37-16-01

Data sheet**JACKPAC
JP TEST**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Approvals**

Approvals



ROHS

Conform

Downloads

Brochure/Catalogue

[CAT 8 SAI 15/16 EN](#)
[FL FIELDWIRING EN](#)

Engineering Data

[EPLAN, WSCAD](#)