

**ESG**  
**ESG-M 9/17 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from the following manufacturers:

- Siemens
- Télémecanique
- ABB
- Beckhoff
- Lumberg
- Tags for all-purpose usage; self-adhesive or clip-on tags, depending on the type

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Please note that these markers are not intended for printing with the SpeedMarking laser.

**General ordering data**

Type	ESG-M 9/17 MC NE WS
Order No.	<a href="#">1027280000</a>
Version	ESG, Device markers x 17 mm, PA 66, Colour: white, pluggable
GTIN (EAN)	4032248753277
Qty.	200 pc(s).
compatible printer	<a href="#">1324380000</a>

**ESG**  
**ESG-M 9/17 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	17 mm	Width (inches)	0.669 inch
Height	9 mm	Height (inches)	0.354 inch
Depth	0.8 mm	Depth (inches)	0.031 inch
Net weight	0.538 g		

**General data**

Application/manufacture	Murr MVP Module	Colour	white
Halogen	No	Material	PA 66
Material colour according to resistance code	9	Number per sheet	40
Operating temperature range	-40...100 °C	UL 94 flammability rating	V-2
Version	pluggable	Width	17 mm

**Classifications**

ETIM 3.0	EC001288	ETIM 4.0	EC001288
ETIM 5.0	EC001288	ETIM 6.0	EC001288
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-29
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>
Software	<a href="#">M-Print PRO configuration file</a>

**Data sheet**

**ESG**  
**ESG-M 9/17 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

