

SAI-M23-SE-L-6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Pinning

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Type	SAI-M23-SE-L-6
Order No.	1170350000
Version	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248962303
Qty.	1 pc(s).

SAI-M23-SE-L-6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	8 g
------------	-----

Temperatures

Operating temperature, max.	125 °C	Operating temperature, min.	-40 °C
-----------------------------	--------	-----------------------------	--------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Standards

Certificate No. (UR)	E344862
----------------------	---------

General data

Coding	none	Conductor O.D.	-
Connection thread	M23	Contact number / diameter	6 x 2 mm
Design	Male	Fire behaviour	V-0
Housing main material	Thermoplastic polyamide PA 6, PBT	Insulation strength	> 10 ¹³ Ω
No. of poles	6	Plugging cycles	> 1000
Rated current	2 mm Kontakt = 28 A	Rated voltage (text)	2 mm Kontakt = 600 V
Type of connection	Crimp connection		

Classifications

ETIM 5.0	EC002635	ETIM 6.0	EC000438
eClass 6.2	27-06-91-90	eClass 7.1	27-06-91-90
eClass 8.1	27-06-91-90	eClass 9.1	27-44-02-05

Product information

Product information	Enclosures, inserts and crimp contacts need to be ordered separately.
---------------------	---

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 8 SAI 15/16 EN FL FIELDWIRING EN
--------------------	---

SAI-M23-SE-L-6**Weidmüller Interface GmbH & Co. KG**


Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com**Drawings****Dimensioned drawing****Technical data**

No. of poles	5 + PE	4/4	
Number of contacts	6	4	4
Contact-ø	mm 2	1	2

6 times male, 2 mm