

**SAIH-CD-2X0.34/0.22-PVC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Weidmüller offers a large and comprehensive range of sensor-actuator cables. We provide both, sensor cables as well as bus and valve cables of various sizes and lengths. If you cannot find a specific product or a product in the desired length, just contact us.

**General ordering data**

Type	SAIH-CD-2X0.34/0.22-PVC
Order No.	<a href="#">1232650000</a>
Version	Bus line, No. of poles: 5, Shielded: Yes, LED: No, Sheath material: PVC, Halogen: Yes
GTIN (EAN)	4050118016383
Qty.	100 m

**SAIH-CD-2X0.34/0.22-PVC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 52 g

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Technical specifications for cable**

Number of poles	5	Wire cross section	2 x 0.34 mm <sup>2</sup> + 2 x 0.22 mm <sup>2</sup>
Outside diameter	7 ± 0.3 mm	Shielded	Yes
Insulation	PVC	Colour coding	white, blue, red, black
Sheath material	PVC	Sheathing colour	black
Halogen	Yes	Temperature range, moving	-10...80 °C
Temperature range, stationary	-40...80 °C	Outer cladding in accordance with UL AWM style	2571 (80 °C)
Suitable for cable carriers	No	Bending radius, min., stationary	5 x cable diameter
Bending radius, min., moving	10 x cable diameter	Acceleration	5 m/s <sup>2</sup>
Speed	180 m/min	Bending cycles	3 Mio
Resistant to welding beads	No	Hybrid cable	No
Irradiation crosslinked	No	Configurable cable length	No

**Classifications**

ETIM 6.0	EC000830	eClass 6.2	27-06-91-90
eClass 7.1	27-06-91-90	eClass 8.1	27-06-91-90
eClass 9.0	27-06-18-05	eClass 9.1	27-06-90-90

**Approvals**

Approvals



ROHS Conform

**Downloads**Brochure/Catalogue [FL FIELDWIRING EN](#)