





a-a SECTION



b-b SECTION



c-c SECTION



技术参数: SPECIFICATIONS

- 适用线规: AWG#24~#30
Applicable wire: AWG#24~#30
- 额定电压: 250V DC/AC (有效值)
Voltage rating: 250V DC/AC (rms)
- 额定电流: 2.5-1.0A
Current rating: 2.5-1.0A
- 耐压值: 800V AC(有效值)
Withstand voltage: 800V AC(rms)
- 工作温度: -25°C~+85°C
Working Temperature: -25°C+85°C
- 绝缘电阻: ≥1000MΩ
Insulation resistance: ≥1000MΩ
- 接触电阻: ≤0.02Ω
Contact resistance: ≤0.02Ω

料号PART NO:

品名 TITLE: PH2.0-T

材料: 磷铜

单位: MM

包装规格: 10K/卷

比例: 1:1

一般公差
GENERAL TOLERANCE
X.X ±0.15
X.XX ±0.05
ANGLE ±1°

日期版次
REVISION

日期
DATE

变更内容
DESCRIPTION


核 准
APPROVALBY

制图:
LI

审核:
LI

核准:
LI

日期:
2010/02/22



6

5

4

3

2

1