

SENTRON, cylindrical fuse link, 14x51 mm, 32 A, gG, Un AC: 690 V



Model	
Product brand name	SENTRON
Product designation	Cylindrical fuse link
General technical data	
Operating class of the fuse link	gG
Size of the fuse link	14x51 mm
Type of voltage	AC
Current / at AC / rated value	32 A
Supply voltage / at DC	250 V
Operating voltage / rated value	690 V
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	3.5 W
Main circuit	
Operating current / Rated value	32 A
Product details	
Product component / striker	No
Mounting position	Any, preferably vertical

Net weight

22 g

Certificates

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F

F

Declaration of Conformity

Test Certificates



EG-Konf.

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW6112-1>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW6112-1>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6112-1

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

