

SITOR cylindrical fuse link, 10 x 38 mm, 16 A, gR, Un AC: 690 V, Un DC: 440 V



Model	
Product brand name	SENTRON
Product designation	SITOR cylindrical fuse link
General technical data	
Operating class of the fuse link	gR
Size of the fuse link	10x38 mm
Type of voltage	AC
Current / at AC / rated value	16 A
Supply voltage / at DC	440 V
Operating voltage / rated value	690 V
Main circuit	
Operating current / Rated value	16 A
Product details	
Product component / striker	No
Mounting position	Any, preferably vertical
Net weight	10 g
Certificates	

#### Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F

F

#### General Product Approval

[Miscellaneous](#)



UR

#### Further information

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC1016-0MK>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NC1016-0MK>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NC1016-0MK](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC1016-0MK)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

<http://www.siemens.com/specifications>



