

DIAZED base DII 25 A 500 V AC DC 500 V AC DC



Model	
Product brand name	SETRON
Product designation	DIAZED fuse system
Design of the product	DIAZED base, head contact/clamp-type terminal
Design of the fuse base	gauge inset
General technical data	
Number of poles	1
Size of fuse system / acc. to DIN EN 60269-1	DIII
Supply voltage	
Current / at AC / rated value	25 A
Supply voltage / at AC / rated value	500 V
Product details	
Product component / Cover	No
Mechanical Design	
Height	70 mm
Width	38.4 mm
Depth	46.6 mm

Net weight	99.56 g
Material / of the enclosure	porcelain

Certificates

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F
F

General Product Approval	Declaration of Con- formity	Test Certificates
---------------------------------	--	--------------------------



KEMA



VDE



EG-Konf.

[Type Test
Certificates/Test Report](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SF1005>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SF1005>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF1005

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



