

DIAZED fuse base size DII Molded plastic, 1-pole touch-protected (BGV A2) Access: Double function terminal Outgoing feeder: Box terminal 25A 500 V AC



Model	
Product brand name	SENTRON
Product designation	DIAZED fuse system
Design of the product	DIAZED base
Design of the fuse base	gauge inset
General technical data	
Number of poles	1
Size of fuse system / acc. to DIN EN 60269-1	DII
Supply voltage	
Current / at AC / rated value	25 A
Supply voltage / at AC / rated value	500 V
Product details	
Product component / Cover	Yes
Mechanical Design	
Height	40 mm
Width	80 mm
Depth	55 mm

Net weight	154 g
Material / of the enclosure	plastic

## Certificates

### Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F  
F

## Declaration of Conformity



EG-Konf.

## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SF1060>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SF1060>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SF1060](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF1060)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



