

DIAZED base DIII 63 A 690 V AC 500 V DC Clamp terminal/saddle terminal



Figure similar

Model	
Product brand name	SETRON
Product designation	DIAZED fuse system
Design of the product	DIAZED base
Design of the fuse base	gauge inset
General technical data	
Number of poles	1
Size of fuse system / acc. to DIN EN 60269-1	DIII
Supply voltage	
Current / at AC / rated value	63 A
Supply voltage / at AC / rated value	690 V
Product details	
Product component / Cover	No
Mechanical Design	
Height	80 mm
Width	46 mm

Depth	47 mm
Net weight	167.5 g
Material / of the enclosure	porcelain

Certificates

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F
F

General Product Approval	Declaration of Conformity	Test Certificates
--------------------------	---------------------------	-------------------



VDE



EG-Konf.

[Type Test Certificates/Test Report](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SF1205>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SF1205>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF1205

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



