

SITOR cylindrical fuse link, 22x58 mm, 32 A, gR, Un AC: 690 V, Un DC: 600 V



Model	
Product brand name	SENTRON
Product designation	SITOR cylindrical fuse link
General technical data	
Operating class of the fuse link	gR
Size of the fuse link	22x58 mm
Type of voltage	AC
Current / at AC / rated value	32 A
Supply voltage / at DC	600 V
Operating voltage / rated value	690 V
Main circuit	
Operating current / Rated value	32 A
Product details	
Product component / striker	No
Mounting position	Any, preferably vertical
Net weight	60 g
Certificates	

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F

F

General Product Approval



UR

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC2232-0MK>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NC2232-0MK>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2232-0MK

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



