



Designation:	17647 101 001	
Battery Requirement:	3 x AAA	
Bulb required:	1 pcs. SMT cool white LED & 1 pcs. COB LED 1 pcs. COB LED	
Luminous intensity:	Spot:	110 lm
	Area:	40 lm
Range:	Spot:	40 m /Area 12 m
	(calculated distance at maximum luminous intensity with an illuminance of 0,25 lux)	
Weight:	54.2 g (without batteries)	
Material:	ABS PC (Polycarbonate) TPR (Thermoplastic Rubber) All contact parts made of aluminium, bronze or nickel plated steel	
Dimensions (mm):	A:	173.3
	B:	30.7
	C:	23.7
Run Time:	Spot:	6 h
	Area:	6 h
Features (Technical):	1 pcs. cool white LED as flashlight & COB cool white LED for worklight Press button (Spot / Area / Off) Strong magnet on pocket clip for hands free Pocket clip IPX4 water resistant 1 meters drop test (with magnetic holder) 10.000 switch cycle life	

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries