



Designation: 17648 101 001
Battery Requirement: 3 x AA
Bulb required: 1 pcs. COB LED

Luminous intensity: High: 230 lm
 Low: 65 lm

Range: High: 22 m
 Low: 12 m
 (calculated distance at maximum luminous intensity with an illuminance of 0,25 lux)

Weight: 155.8 g (without batteries)

Material: ABS
 PC (Polycarbonate)
 All contact parts made of aluminium, bronze or nickel plated steel

Dimensions (mm): **A: 118.8**
B: 61.7
C: 68.9

Run Time: High: 6 h
 Low: 35 h

Features (Technical): Super bright COB cool white LED
 Push switch (High/Low/Off) on hand for easy of use
 Strong magnet on pocket clip for hands free
 180° swivel head
 IPX4 water resistant
 2 meters drop test
 10.000 switch cycle life



No publication or circulation of data to third parties without consent of VARTA Consumer Batteries