



2 Port DVI-D Single Link, USB 2.0 & Audio KVM Switch Compact

Part No.: 42341

Description

- Switches DVI-D USB Keyboards & Mice, USB 2.0 peripherals plus audio devices
- Supports DVI-D single link resolutions up to 1920x1200
- Hotkey function - KVM only, Audio only or KVM & Audio
- Supports USB Keyboards & Mice, Game Pads & Multimedia Keyboards
- Supports wired and wireless connections
- Additional USB accessories can be attached using a USB Hub (not included)
- Features a LED status indicator on the switch and taskbar icon (PC & Mac)
- USB 2.0 speeds up to 480Mbit/sec
- Windows 2000/XP/Vista/7/8, Linux (eg. Ubuntu 7.10) & Mac OS 10.5.x.
- Cable length 1.5 metres
- 2 year warranty

Please Note - Not for use with HDMI monitors, graphics cards, notebooks or PCs as Deep Color & 3D are not supported, use our HDMI KVM Switch 42340

Featuring integrated cables for quick installation this KVM switch allows two DVI-D equipped PCs to be controlled from a single keyboard, mouse and monitor. Simply connect the cables to your computers and attach a keyboard, mouse and monitor to the switch and your ready to start. The two additional 3.5mm audio ports allow users to connect headphones and a microphone while extra USB peripherals can also be attached with the addition of a USB hub.

Switching functions

- Shift "Quick Switch" on the KVM Switch with 90cm Cable
- Hotkey change-over via 'button roll'
- Hotkey change-over via 'CTRL + ALT + 'configurable key' (PC & Mac)
- Switching via software icon in the taskbar (Windows & Mac)

- The DVI-D, USB 2.0 and audio ports switch simultaneously

If needed, the audio ports can be bound to a port using the included software (PC & Mac)

Technical details

Specifications

- AV Interface: DVI-D
- Console Interfaces: USB
- Interface Standard: HDVI-D (Single Link), USB 2.0
- Maximum Resolution: 1920x1200@60Hz
- HDCP Support: 1.4
- Supported Audio: Analog Stereo
- Separate Audio Ports: 2 x 3.5mm (Female)
- Serial Interface: -
- Console Number: 1
- Max Number PC/Server: 2
- Cascadable: -
- Switching Method: Port Buttons, Hotkey Switching & Software
- 19" Rack Mountable: -
- Special Features: Supports USB 2.0 Hubs And Device Sharing

Connectors

- Console Interfaces: DVI (Female), USB 2.0 Type A (Female), 2 x 3.5mm (Female)
- PC/Server Interfaces: 2 x DVI-D (Male), USB 2.0 Type A (Male), 2 x 3.5mm (Male) Integrated Cables
- Other Interfaces: -
- Power: -

Physical Properties

- Dimensions WxDxH: 85x55x25mm (3.35x2.17x0.98in) Cable length 0.9m (2.95ft)
- Housing Material: Plastic
- Net Weight: 0.46kg (1.01lb)
- Operating Temperature: 0°C - 50°C (32°F - 122°F)
- Storage Temperature: -20°C - 60°C (-4°F - 140°F)
- Humidity: 0~90% RH (non-condensing)
- Power Requirements: Powered by USB
- Colour: Black

Miscellaneous

- Packaging Type: Carton box
- Packaging Dimensions: 160x75x165mm (6.3x2.95x6.5in)
- Gross Weight: 0.6kg (1.32lb)
- Warranty (Years): 2

- Certificated: CE, FCC, RoHS & REACH

Package Content

- KVM Switch (KVM + Audio Cables Integrated)
- LINDY Manual
- CD with Software

Purchasing Information

- No.: 42341
- EAN: 4002888423410

© LINDY 2019